

# 30MM SELECTOR SWITCH 2 POSITION

9001KS25B

EAN Code: 3389118039834

## Main

Range of product	Harmony 9001K	
Product or component type	Head for selector switch	
Device short name	К	
Type of operator	spring return	
Operator profile	Black standard knob	

## Complementary

Bezel material	Metal	
Mounting diameter	30 mm	
Operator position information	2 positions	
Contacts type and composition	Without contact block	
Device presentation	Basic element	
Cap/operator or lens colour	Black	
Operator profile	Standard handle	
Type of operator	Spring return	
Size	30 mm	
Return	Left to right	
Cam profile	5	

## **Environment**

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13	
Product certifications	CE UL listed file E42259 CCN NKCR	
	CSA LR24590 class 3211 03	

## **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.08 cm
Package 1 Width	5.842 cm
Package 1 Length	7.112 cm
Package 1 Weight	122.47 g

# **Logistical informations**

Country of origin

FR

## **Contractual warranty**

Warranty

18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

#### **Use Better**

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ae0c4eb9-0bfb-40a4-851f-5c619fbe777d
REACh Regulation	REACh Declaration

#### **Use Again**

○ Repack and remanufacture	
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

### **Alternative**







