

Features

- Double plug
- British Type G
- Urea Formaldehyde
- Screwed faceplate
- IP20 rated
- Meets BS standards

RS PRO UK 2 Gang Wall Socket

RS Stock No.: 775-8065



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

A 230V double gang plug socket suitable for Type G (British) plugs.

The plug socket is made from urea formaldehyde, a durable resin that offers low water absorption. Supplied with two zinc-plated fixing screws and three white plastic screw head caps. The socket has two gangs and is switched, so each plug has its own power control.

Meets British fixing standards for electrical components.

General Specifications

Socket Type	BS 1363
Number of Gangs	2
Colour	White
Switched	Yes
Socket Type	Type G British
Indoor/ Outdoor	Indoor
Mounting Style	Flush Mount
Material	Urea Formaldehyde
Terminal Type	Switched
Switch Style	Rocker
Earth Terminal	Yes

Electrical Specifications

Number of Poles	1
Current Rating	13A
Voltage Rating	230V

Mechanical Specifications

Minimum Box Depth	25mm
Overall Height	146mm

Overall Width	86mm
Overall Depth	33mm
IP Rating	IP20

Approvals

Standards	BS 1363
-----------	---------