

Parker Product Datasheet



The Maxiflow Series is a range of spin-on filters designed to provide low cost quality protection for hydraulic or lubrication systems.

Maximum pressure 10 bar. Maximum flow 360 l/min.

PART NUMBER: MXA2310CBU4RG201

FLOW RATE: 0 to 130 l/min

CONNECTION TYPE: G1¼

SEAL MATERIAL: Nitrile

FILTER ELEMENT TYPE: 10C Cellulose

MICRON RATING: 10 µm

OPTIONS: Standard

INDICATOR TYPE: Visual

BYPASS VALVE PRESSURE RATING: 0.2 bar