



### Main

Range	Acti 9
Product name	Acti 9 SBI
Product or component type	Fuse-disconnector
Device short name	SBI
Poles description	1P

### Complementary

[In] rated current	32 A 40 A 50 A 63 A 80 A 100 A 125 A
Fuse curve	AM GG
Fuse size	22 x 58 mm
[Ue] rated operational voltage	690 V AC
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	4
Connections - terminals	Screw clamp terminals 1 cable(s) 2.5...25 mm <sup>2</sup> rigid Screw clamp terminals 1 cable(s) 2.5...25 mm <sup>2</sup> flexible
Tightening torque	3.5 N.M

### Environment




Standards	IEC EN 60947-3
Pollution degree	3
Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-40...80 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	186 G
Package 1 Height	3.5 Cm
Package 1 width	7.7 Cm
Package 1 Length	12.8 Cm
Unit Type of Package 2	BB1
Number of Units in Package 2	6

Package 2 Weight	1.185 Kg
Package 2 Height	13 Cm
Package 2 width	8 Cm
Package 2 Length	21 Cm
Unit Type of Package 3	S03
Number of Units in Package 3	54
Package 3 Weight	11.02 Kg
Package 3 Height	30 Cm
Package 3 width	30 Cm
Package 3 Length	40 Cm

### Offer Sustainability

EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	<b>Commercialised</b>
-----------------------	-----------------------