



ENGLISH

RS Pro Datasheet

Grey, smooth, flexible hose with BfR-approved inner rubber layer. For hot and cold beverages, e.g. beer, wine, fruit juice and milk. Inner and outer surfaces resistant to vegetable and animal oils.

Certification can be supplied.

It is recommended that new hoses are flushed with 5% soda solution before use. Flushing after use is also recommended.

Normally installed using stainless connectors or hose clamps.

Please contact Codan for further information.

Application: Food / Beverages

Standard Length: 25 metres

Working Temperature: -20°C to 100°C

Inside: NBR

Colour: White

Reinforcement: PVA

Outside: NBR/PVC

Colour: Grey

Standards: BfR, kap XXI, kat. 2. EU Reg. No.: 1935/2004 & 2023/2006

Inside dia. (mm)	Outside dia. (mm)	Working Pressure BAR	Burst Pressure BAR	Bend Radius (mm)	Weight (g/m)
6,3	15,0	20	60	60	203
9,5	18,5	20	60	74	275
12,7	21,6	20	60	86	333
15,9	25,1	20	60	100	411
19,1	28,6	20	60	114	490
22,3	32,3	20	60	130	592
25,4	35,6	20	60	142	673