

370033161

Stainless steel industrial enclosure IGSN A2 300 x 300 x 167 mm

Stainless steel industrial enclosure IGSN A2 300 x 300 x 167 mm

Drawing 3D Data

Technical data

Height	300 mm
Width	300 mm
Depth	167 mm
Material	Stainless Steel
Material quality	1.4301/304
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK09
temperature min.	-60 °C
temperature max.	175 °C
Seal material	VMQ-(silicone)
Flame spread, sideways	HL 3
Rate of head dispersion	HL 3
Smoke gas concentration	HL 3
Other versions on request	EMV
Approvals	LR (Lloyd's Register), UL (508A)

Commercial data

Country of origin	IN
Order unit	1 Piece
Customs tarif number	85369095
Weight	4.59 kg
GTIN	4057624608521


ETIM classification

ETIM 8	EC000058


ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de


Accessories



100110440
Mounting plate for 37.3030xx




100614360
DIN rail 35/7,5 for 37.301508



100620210
Earth rail for 37.301508




100681210
Protective conductor busbar for 34.30xxx /xx.0033xx



370100030
Flange size 3 - 130x260x3



371050000
Stainless steel external mounting brackets



379900010
Mounting set for Stainless-steel enclosures