



## Datasheet

# RS PRO Automatic cable reel H05VV-F 3G1.25mm<sup>2</sup> 16(15.6+0.4)+2(1.7+0.3)m,BS Plug and Socket

Stock number: 171-7879

EN



### Electrical Specification:

Rated voltage: 230 V ac 50Hz  
Rated power (Full-reeled): 1000W  
Rated power (Unreeled): 3000W  
Re-settable thermal protection @56+/-5°C

### Special Feature:

Heavy duty industrial cable reel with spring load.  
High quality engineer PP housing .  
Plug and Socket Type : BS  
Input line: H05VV-F,3G1.25mm<sup>2</sup>,2m length (1.7m net cable length,0.3M cable inside cable reel) .  
Output line: H05VV-F,3G1.25mm<sup>2</sup>,16m length (15.6m net cable length,0.4M cable inside cable reel) .  
Pull the power cords and stop some location as you want.  
Wall bracket 180 degree swivel.  
Over current or temperature protector.  
Dimensions: 380x163x330mm