

2U DIN Rail Kit for Standard 19" Rack - Adjustable Depth Rackmount DIN Rail with Top Hat, Mini, G Rails, 27lbs/12.5kg Weight Capacity

**Product ID:** ADJDINKIT



The ADJDINKIT Adjustable Rack Mount DIN Rail Kit with Top Hat/Mini/G Rails makes mounting your DIN-rail equipment in a 19-inch server rack/cabinet or wall plate simple, without wasting space due to special bracket requirements for each piece of equipment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

This 19-inch DIN Rail Mounting Kit includes the three most commonly used DIN rail systems: Top-Hat, Miniature Top-Hat, and G-Type.

Backed by a StarTech.com Lifetime Warranty.

## Certifications, Reports and Compatibility

## Applications

- Install DIN Rail mountable hardware into a standard 19" rack or cabinet
- Two ADJDINKIT's can be used in the same U height, facing each other and mounted on both front and back rails

## Features

- **STANDARD COMPATIBILITY:** With its universal design, this DIN rail mount fits standard 19in wide server racks or cabinets and takes up 2U of space; Max weight capacity is 27.5lb (12.5kg)
- **HEAVY DUTY CONSTRUCTION:** The DIN rail kit is constructed using solid cold-press steel, keeping your valuable

equipment securely mounted

- **VERSATILE USE:** This DIN rail kit offers adjustable DIN-rail depth to accommodate a wide range of products, including DIN-rail media converters, industrial PoE switches, audio and AV equipment
- **WIDE COMPATIBILITY:** This rackmount rail kit includes three types of DIN rails (top-hat, miniature top-hat, and g-type), making it compatible with nearly all DIN rail equipment
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this DIN rail mounting kit is backed for life, including free lifetime 24/5 multi-lingual technical assistance

---

#### Hardware

Warranty	Lifetime
Frame Type	Steel
U Height	2U
Cable Management	No

---

#### Physical Characteristics

Color	Black
Internal Width	16.4 in [41.7 cm]
Internal Height	3.3 in [85 mm]
Internal Depth	8.7 in [22.2 cm]
Product Length	9.9 in [25.2 cm]
Product Width	19.0 in [48.3 cm]
Product Height	3.5 in [8.9 cm]
Weight of Product	4.4 lb [2.0 kg]
Maximum Mounting Depth	8.7 in [22.2 cm]

---

#### Packaging Information

Package Quantity	1
Package Length	22.0 in [56.0 cm]
Package Width	12.8 in [32.5 cm]
Package Height	5.3 in [13.5 cm]

Shipping (Package) Weight	5.8 lb [2.6 kg]
------------------------------	-----------------

---

#### What's in the Box

Included in Package	1 - Din Rail mounting brackets
	1 - Top-Hat Din Rail
	1 - Miniature Top-Hat Din Rail
	1 - G-Type Top-Hat Din Rail
	4 -
	4 - M5 Screws
	4 - M5 Cage Nuts
	4 - Carriage Bolts
	4 -
	4 - DIN rail mounting Screws
	4 - Wing Nuts

---

***\*Product appearance and specifications are subject to change without notice.***