



Product data sheet

Power tools for trade & industry

Cordless Jobsite Light

PRO GLA 18VH-7500



360° hybrid area light with 7500 Lumen

The most important data

Battery voltage, works with	18.0 V
Luminous flux	7,500 lm
Weight excl. battery	4.1 kg

Part Number 0 601 4A5 001

Technical data

Technical data

Weight excl. battery	4.1 kg
Luminous flux	7,500 lm
Number of brightness levels	3
Packaging dimensions (width x length x height)	225 x 225 x 366 mm
Battery voltage, works with	18.0 V

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Outstanding performance with 7500 lm max luminous flux, 3 brightness levels and 180/360° modes
- Hassle-free runtime thanks to hybrid power for corded or cordless operation
- Convenient fast-charge for USB-C®-powered devices via integrated USB-C® port
- Optimal light distribution thanks to large, robust hook in base and tripod mounting options
- Always in the know thanks to intuitive HMI feature indicating the battery state of charge, brightness setting and 180°/360° function

**HEAVY
DUTY****7500
LUMEN****AREA LIGHT****6h
RUNTIME 8.0 Ah****USB-C®****50%
100%**

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

