










Three optional battery choices	22Ah		36Ah		18Ah	
	 14K	 9.5kg	 14K	 7.0kg	 14K	 5.7kg
Battery	12V 22Ah SLA		16.4V 36Ah Li-ion		14.8V 18.2Ah Li-ion	
Charge time	8h		12h		7h	
Product weight (kg)	9.5		7.0		5.7	
Boxed weight (kg)	11.8		7.6		6.3	
Run time	30h 11h 4h 3h30 1h40		72h 14h 6h 6h 3h		36h 7h 3h 3h 1h30	
5 Light modes	1000 3500 6000 flashing 14000		3500 6000 flashing 14000		3500 6000 flashing 14000	
Part No.	NSSOLARISLITE14K		NSSOLARISLITELI-ION36AH14K		NSSOLARIS-LI-ION-14k-2AMPH	
CAT/PAD No.			0111/108165			

Optional	 6K		 6K	
	 14h 2h30 7h	 18h 9h30 3h30		
Run time	14h 2h30 7h		18h 9h30 3h30	
3 Light modes	flashing 3500 6000		flashing 3500 6000	
Part No.	NSSOLARISLITE6K		NSSOLARIS-LI-ION-6K-2AMP	

SOLARIS LITE / LITE LI-ION	
Boxed size (mm)	L460 x D320 x H280
Head size (mm)	L300 x D58 x H248
Case size (mm)	L250 x D180 x H140

OPTIONAL EXTRAS
Optional colour lenses: red, green, blue, yellow
Car adaptor / 5m extension lead
Magnetic base / mounting clamp
Vehicle charger / extension lead / stability legs.