

Hot air tool - Professional Line

PRO HM 2120 E Carwrapper-Set

EAN 4007841 089658

Article number 089658



series 5

2200 W

2200 W Output



80 – 630 °C



9 stage temperature
adjustment



150 - 500 l/min.



3 air volume levels



Suitable for pluggable
nozzles



VDE



CE

Function description

Experts in vehicle wrapping. Electronically controlled hot air tool HeatMatic 2120 E with 7.5 m cable. 2200 W, infinitely adjustable temperature from 80 – 630 °C, airflow rate adjustable from 150 – 500 l/min in 3 stages. Incl. temperature scanner HL Scan for absolute temperature safety.

Technical specifications

Temperature	80 – 630 °C
Airflow rate	150 – 500 l/min
Temperature setting	Continuous
Settings made via	Thumbwheel
Temperature display	Thumbwheel with labelled settings
Airflow control	Settings
Programming function	No
Loc function	No
Residual heat indicator	No
Cool function	No
Motor, type	Brush motor
Heating element	Ceramic heating element
Mains power supply	220 – 230 V / 50 – 60 Hz
Function, hanger	Yes
Function, life expectancy, motor	750 h
Function, life expectancy, heating element	600 h

Replaceable heating element	No
Restart protection	No
Temperature scanner	Yes
Fine dust filter	No
Thermal cut-out	Yes
Thermostat	Yes
ESD	No
Nozzle receiver, type	34
Cord length	7.5 m
Dimensions (L x W x H)	253 x 87 x 200 mm
PU1, net weight	1,073 kg
Manufacturer's Warranty	1 year
PU1, EAN	4007841089658
Scope of delivery	incl. temperature scanner HL Scan
Output	2200 W
Product category	Hot air tool

<https://www.steinell.de>

Subject to technical modifications

03.2025 Page 1 from 2

Hot air tool - Professional Line

PRO HM 2120 E Carwraper-Set

EAN 4007841 089658

Article number 089658



Accessories

EAN 4007841 053963

Hot Air Tool Guard Cage HL 1820 S - HG 2320 E

EAN 4007841 084189

Plastic squeegee - Alcantara

EAN 4007841 009601

Flexible hot air tool stand with suction pad foot