



Main

Range	PowerLogic
Product name	CT
Product or component type	Current transformer
Secondary current	5 A
Accuracy class	Class 0.5 at 4 VA Class 1 at 7 VA
[In] rated current	200 A

Complementary

Current transformer type	Tropicalised for busbar and cable
Current transformer ratio	200/5
[Ith] conventional free air thermal current	12 kA
Dynamic withstand current	2.5 Ith
Maximum safety factor	5
[Ue] rated operational voltage	< 720 V AC 50/60 Hz
[Ui] rated insulation voltage	3 kV
Mounting mode	Clip-on By screws Insulated locking screw
Mounting support	DIN rail Busbar Mounting plate
Width	56 mm outside:
Height	80 mm outside:
Depth	43 mm frame: 63 mm total:
Diameter	27 mm
Net weight	0.318 kg

[Uimp] rated impulse withstand voltage	3 kV
Electrical insulation class	Class B
Cable outer diameter	27 mm
Opening of bars	32.5 x 10.5 25.5 x 15.5
Sealing	Without

Environment

Standards	IEC 61869-2 VDE 0414
Product certifications	EAC CE
IP degree of protection	IP20
Relative humidity	0...95 %
Ambient air temperature for operation	-25...60 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins