

111.10.063 1 bar G1/4B

Bourdon tube pressure gauges,model 111

Item number: 9013644

Quantity: 1 pcs.

Order code: 111.10-C-BG310Z-GB-UAZZNZ4Z-Z-ZZZZ 1SBZAAA3AA3
DIAL-IAZ1ZZZZZZZZZ1Z- 1Z1ZZ9ZZZZ
LABEL-E01DE-ZZZZZ

Overview: 111.10.063 1 bar G1/4B
Connector location: lower mount
Case: black plastic
class 2.5
Window: plastic, clear
Pointer: plastic, black
standard packing
Dial: plastic, white, with stop-pin
stop-pin at zero
EN 837-1 *Cl.2.5* *WIKA*

Details: Bourdon tube pressure gauges,model 111
Model: 111.10
Specifications according to data sheet
Model: 111.10 standard bottom
Nominal size: 063 mm
Unit of outer Scale: bar
Measuring range: gauge pressure range
Scale range: 0...1 bar
Process connection: G 1/4 B
Connector location: lower mount
Case: black plastic
Window: plastic, clear
Accuracy class: class 2.5
Overpressure safe: standard
Ingress protection: Standard
Pointer: plastic, black
Packaging: standard packing
Process connection surface area: brass
Dial: plastic, white, with stop-pin
Specifications according to data sheet: PM 01.01
Dial description:
Pressure Gauge Standard: International (standard Europe)
color for 1.scale (outside): black
dial background: White
Manufacturer logo: *WIKA*
stop pin on dial: at zero

Date: 22/01/2024



norm-mark on dial: *EN 837-1*

accuracy class on dial: *Cl.2.5*