

666HS
ZERO-RESET click-type torque wrench for right-hand tightening, with H-SAFE tethered system
ISO 6789
With H-SAFE tethered system

The torque wrench, Beta 666 ZERO-RESET, is ideal for controlled tightening of screws and bolts. 100% Italian-made, the wrench does not require releasing tension after use! Reaching of the set torque is indicated by a mechanical click that can be heard and touched. Torque accuracy: $\pm 3\%$.

	art.	Nm	Kgfm	lbf.ft	■	D mm	A mm	L mm	LC system	g
006664705	666HS/5	10÷50	1÷5	7÷37	3/8	30	33	342		680
006664710	666HS/10	20÷100	2÷10	15÷75	3/8	30	33	385		760
006664721	666HS/20LC	40÷200	4÷20	30÷150	1/2	42	43	471	•	1020
006664731	666HS/30LC	60÷300	6÷30	50÷220	1/2	42	43	600	•	1270

