



Product data sheet

Power tools for trade & industry

Screwdriver

VDE Screwdriver SL6.5x125

Insulated, simple, convenient – Bosch Professional VDE SL6.5x125 screwdriver

The most important data

Part Number 1 600 A02 NC4



Technical data

Technical data

Material	S2
Profile	SL
Blade width	6.5 mm
Shaft length	125 mm
Blade diameter	6.5 mm
Blade thickness	1.2 mm
Handle diameter	38 mm
Weight	0.115 kg
Anti roll-off design	+
Soft grip handle	+
Ergonomic grip	+
Tool finder	+
Slim blade insulation	+
VDE	+
Packaging dimensions (width x length x height)	63 x 307 x 35 mm
Maximum voltage	1,000 V

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Tested up to 10,000 volts and VDE-certified up to 1,000 volts according to DIN EN/IEC 60900
- Precise and durable with slim shaft and robust tip for fitting accuracy
- Hand-friendly and comfortable to use thanks to soft grip and ergonomic design



SOFT GRIP



ERGONOMIC



ANTI-ROLL



GS



DURABLE TIP



SAFETY



1.000 V



SLIM SHAFT



DIN EN/IEC 60900