

ENGLISH

Datasheet

RS Pro HSS M10 Spiral Point Thread Tap, 80 mm length

RS Stock No: 455-918



Product Details

RS Pro spiral point thread tap has HSS construction. This 80 mm long tap produces M10 size threads. The straight flute supplemented by an angular cutting point leaves the flutes clear of swarf for a free coolant flow. It has blue steam tempered finish to reduce friction and induce fine thread finish.

Features and Benefits

- Precision HSS taps for machine tapping
- Can be used for hand tapping without need of a lead tap
- Designed with a straight flute supplemented by an angular cutting point leaves the flutes dear of swarf for free coolant flow




ENGLISH


Specifications:


Material	HSS				
Overall Length	80 mm				
Pitch	1.5 mm				
Shank Diameter	10 mm				
Shank Type	Plain				
Thread Size	M10				
Thread Standard	Metric Coarse				
Type	Spiral Point				
Finish	Blue Steam Tempered				
Number of Flutes	3				
Standards Met	ISO				
Tapping Drill Size	8.5 mm				
Thread Length	24 mm				



ENGLISH







Remarks:
- Material: HSS M2

RS MANUFACTURE			OVERALL	MAX	SHANK	SQUARE DETAILS		NO. OF	TAPPING
STOCK	PART NO.	DESIGNATION	LENGTH(mm)	THREAD	DIA.	SQUARE	SQUARE	FLUTES	DRILL
NUMBER	TAKTINO.			LENGTH(mm)	(mm)	LENGTH(mm)	A/F(mm)		SIZE(mm)
455936	T11300200	M2X0.40	41	8	2.5	4	2	2	1.6
455908	T11300250	M2.5X0.45	44.5	9.5	2.8	5	2.24	2	2.05
455902	T11300300	M3X0.50	48	11	3.15	5	2.5	3	2.5
455891	T11300350	M3.5X0.60	50	13	3.55	5	2.8	3	2.9
455895	T11300400	M4X0.70	53	13	4	6	3.15	3	3.3
455992	T11300500	M5X0.80	58	16	5	7	4	3	4.2
455930	T11300600	M6X1.0	66	19	6.3	8	5	3	5
455920	T11300800	M8X1.25	72	22	8	9	6.3	3	6.8
455918	T11301000	M10X1.5	80	24	10	11	8	3	8.5
455958	T11301200	M12X1.75	89	29	9	10	7.1	3	10.3
455986	T113002BA	2BA	58	16	5	7	4	3	3.9
455946	T113004BA	4BA	50	13	3.55	5	2.8	3	2.95
455942	T113006BA	6BA	44.5	9.5	2.8	5	2.24	2	2.3
455952	T113008BA	8BA	44.5	9.5	2.8	5	2.24	2	1.75
455968	T1130 1/4UNC	1/4-20UNC	66	19	6.3	8	5	2	5.1
455964	T1130 3/8UNC	3/8-16UNC	80	24	10	11	8	3	7.9
455914	T1130 5/16-UNC	5/16-18UNC	72	22	8	9	6.3	3	6.5
455980	T113002UNC	2-56UNC	44.5	9.5	2.8	5	2.24	2	1.8
455970	T113004UNC	4-40UNC	48	11	3.15	5	2.5	2	2.25
455974	T113006UNC	6-32UNC	50	13	3.55	5	2.8	2	2.8
455924	T113010UNC	10-24UNC	58	16	5	7	4	2	3.8