

920U
Gear lock hand sockets, 1/2" female drive, chrome-plated


g

	art.	 mm	"			Ø mm	L mm	Ø1 mm	A mm	 g
009201710	920U 10	10	3/8	E12	M12	15	38	22	8	49
009201711	920U 11	11	7/16	E14	M14	16	38	22	8	50
009201712	920U 12	12	15/32	E16		18	38	22	9	54,3
009201713	920U 13	13	1/2		M16	19	38	22	10	55,6
009201714	920U 14	14	9/16	E18	M18	20	38	22	11	57,5
009201715	920U 15	15	19/32			22	38	21	11	62,5
009201716	920U 16	16	5/8	E20		22	38	21	11	71,5
009201717	920U 17	17				24	38	22	12	73
009201718	920U 18	18		E22		26	38	23	13	78
009201719	920U 19	19	3/4	E24		26	38	23	13	83,5
009201720	920U 20	20	25/32			28	38	25	13	98,5
009201721	920U 21	21				28	38	25	14	98,8
009201722	920U 22	22	7/8			30	38	26	15	110
009201724	920U 24	24	15/16			32	38	28	17	144
009201727	920U 27	27	1.1/16			36	42	30	19	174
009201730	920U 30	30	1.1/8			40	44	34	21	240
009201732	920U 32	32	1.1/4			42	44	36	23	265

