

CONTACTUM



Make the switch

2 Gang 2 Way 10AX Switch + Back Box - Metalclad, White Insert

Stock code: CLA3722



Technical

Associated standards:	BS EN 60669-1
Ambient operating temperature:	-5 to 40°C (24hour average not exceeding 25°C)
Base material:	Thermoset
Face plate material:	steel
Fixing screws:	2 x M3.5
IP rating:	IP2X
Maximum installation altitude :	2000m
Minimum switch contact gap :	3 mm
Nature of supply:	AC
Operational testing :	30000
Rated current:	10AX
Rated frequency:	50-60Hz
Rated voltage:	220-250V
Switched poles:	1 pole
Terminal capacity :	3 x 1.0mm 3 x 1.5mm 1 x 2.5mm

General

Face plate finish:	metal
Insert colour:	white
Number of switches:	2
Rocker finish:	white moulded
Switching operation:	2 way

Technical: +44 (0) 208 208 7414 **Sales:** +44 (0) 208 208 7419 **E-mail:** sales@contactum.co.uk