

Features

- Flexible and durable H03VVH2F2X0.75-pvc cable
- European plug XVI EN50075 2.5A-250v
- Moulded IEC -C7 Connector
- Fully moulded connectors for strength and durability
- Integrated strain relief for connection support and protection

RS PRO 1.8m Power cable C7, IEC to XVI EN50075 2.5A 250 V

RS Stock No: 0558923



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- RS PRO Power cable in black colour, has a straight C7(fig.8) connector on one end and a European plug type XVI on the other end and it is 1.8m long current rated for 2.5A and voltage rated for 250 v. The power cord is designed for environments in which an earthing is not required such as in double insulated devices, for example when audio interference/ noise is caused by the earthing is a concern.

General Specifications

Connector A	C7, IEC Female – Straight EN60320 /C7
Connector B	XVI EN50075 Male – Straight
Sheath Colour	Black
Material	PVC
Applications	Household Entertainment (TVs, Satellite boxes, routers etc.) Audi / hi-fi equipment, any environment when earthing is not required.

Mechanical Specifications

Length	1.8m
--------	------

Electrical Specifications


Power Cord Rating	2.5A - 250V
Visual Inspection	100%
Electrical Test	100%
High pot test wire to wire	3.000Vac for 2 sec.
Continuity test	20Aac to line and neutral
Polarity test	no
Skin high pot test	6.000Vac line to skin

Protection Category

Environmental Conformity	Eu-Directive 2002/96/EC (WEEE)
	Eu-Directive 2003/11/EC (Council Directive 76/769/EEC)
	Eu-Directive 2002/95/EC (RoHS-Compliant)

Approvals

C7 CONNECTOR	ENEC, CE
XVI	ENEC, CE
Cable	Harmonised <HAR>, OVE



All dimensions in mm