

Datasheet

## Conquer Cartridge Fuse, T, 0.1 A, 5 x 20 mm

RS Stock Number: **668-5988**

Part Number: **VBS USL 250mA 250V (05)**



### Product Details

Conquer cartridge fuse is current rated for 0.1 A. This glass bodied, T-speed fuse is used as supplementary protection in appliance or utilisation equipment to circuits.

## Specifications:

|                                               |                                          |
|-----------------------------------------------|------------------------------------------|
| Body Material                                 | Glass                                    |
| Breaking Capacity (at Maximum Voltage Rating) | 35 A                                     |
| Current Rating                                | 0.1 A                                    |
| Diameter                                      | 5.2 mm                                   |
| Fuse Speed                                    | T                                        |
| High Rupture Capacity                         | No                                       |
| Includes Indicator                            | No                                       |
| Maximum Operating Temperature                 | +125°C                                   |
| Minimum Operating Temperature                 | -55°C                                    |
| Operating Temperature Range                   | -55 to +125°C                            |
| Overall Dimensions                            | 5.2 x 20 mm                              |
| Overall Length                                | 20 mm                                    |
| Resistance                                    | 10.500 $\Omega$                          |
| Size Designation                              | Miniature                                |
| Voltage Rating                                | 250 V ac                                 |
| Standards Met                                 | CSA Certified, UL Listed, RoHS Compliant |
| UL File Number                                | E82636                                   |