



ENGLISH

Datasheet

Stock No: 534-294

# RS Pro Insulated Crimp Blade Terminal 17.6mm Blade Length, 22 → 16 AWG, Red



## Product Details

### RS Insulated Crimp Blade Terminals

A range of insulated crimp blade terminals made from copper with flared vinyl insulation. These insulated crimp blade wire connectors are colour coded for use with different wire sizes.

Red 0.5 - 1.5 mm<sup>2</sup>

Blue 1.5 - 2.5 mm<sup>2</sup>

Yellow 2.5 - 6.5 mm<sup>2</sup>

### RS Pro Range

| Conversion table |         |
|------------------|---------|
| M3 / 6 BA        | M5/ 2BA |
| M3.5/ 4BA        | M6/ 0BA |
| M4/ 3BA          |         |

| Wire Sizes  |                           |
|-------------|---------------------------|
| Mini Yellow | 0.2 - 0.5 mm <sup>2</sup> |
| Red         | 0.5 - 1.5 mm <sup>2</sup> |
| Blue        | 1.5 - 2.5 mm <sup>2</sup> |
| Yellow      | 2.5 - 6.5 mm <sup>2</sup> |

| Technical Specification |        |
|-------------------------|--------|
| Temperature rating      | +70°C  |
| Body Material           | Copper |
| Body Plating            | Tin    |



ENGLISH

## Specifications:

|                     |             |
|---------------------|-------------|
| Gender              | Male        |
| Wire Size           | 22 → 16 AWG |
| Insulation          | Insulated   |
| Shrouded            | Unshrouded  |
| Insulation Material | Vinyl       |
| Colour              | Red         |
| Overall Length      | 28mm        |
| Inner Diameter      | 4.3mm       |
| Blade Length        | 17.6mm      |
| Blade Width         | 2.5mm       |
| Contact Material    | Copper      |
| Contact Plating     | Tin         |