



ENGLISH

Datasheet

Stock No: 297-0046

# RS Pro G 1/4 Pressure Switch, 0.2bar to 2.5 bar



## Product Details

### F4 Series

Pneumatic adjustable pressure switches from RS. These pressure switches turn air pressure into an electrical signal once a set pressure is reached. Adjustment is via a screw on top of the fitting and can be easily installed into your pneumatic installations.

Preset pressure is adjusted by rotating a screw, located in the centre of the switch, clockwise to increase pressure and anti-clockwise to decrease pressure

DIN 43650 connector

Fixed hysteresis: 15% of set value

Can be set for rise or fall

## Specifications:

Minimum Operating Pressure	0.2bar
Maximum Operating Pressure	2.5 bar
Pressure Type	Positive Pressure
Connection	G 1/4
Type	Adjustable
Voltage Rating	250V ac
Connection Thread Size	1/4 in
Manufacturer Series	F4
Contact Operation	Normally Closed, Normally Open
Connection Thread Standard	G
Minimum Operating Temperature	-25°C
Maximum Operating Temperature	+85°C
IP Rating	IP65
LED Indicator	No