

Eaton 12OHGMA71

Catalog Number: 12OHGMA71

Oil fuse-link, medium voltage, 71 A, AC 12 kV, BS2692 F02, 359 x 63.5 mm, back-up, BS, IEC, ESI, with striker

General specifications



Product Name	Catalog Number
Eaton Bussmann series medium voltage oil fuse	12OHGMA71
	EAN
	5027590432825
Product Length/Depth	Product Height
359 mm	63.5 mm
Product Width	Product Weight
63.5 mm	2.6 kg
Compliances	Certifications
BS 2692-1	IEC Rated
ESI 12-8	IEC60282-1
	KEMA

Product specifications

Type

fuse

Application

protection of primary side transformer, and oil-filled fuse switch combination unit

Amperage Rating

71 A

Fuse indicator

with striker

Fuse size

63.5 x 359 mm

Breaking capacity

40 kA

Installation technique

Oil

Performance Cat According To IEC 60282-1

Back-up

Product application

Primary side transformer protection

Rated frequency - max

60 Hz

Rated frequency - min

50 Hz

Release characteristic

Other

Standard

British Standard

Utilization category

Other

Voltage type

AC

With striker

Yes

Fuse diameter

63.5 mm

Resources

Technical service bulletins

Datasheet - 12OHGMA71

Joule integral (I²T) - max operating

3.9 x 10⁴

Joule integral (I²T) - min pre-arcing

2 x 10³

Resistance

16.6

Class

Class back-up

Barrels

1

Construction type

F02/BS 2692

Fuse shape

Cylindrical

Interrupt rating

40 kAIC

Construction size

63.5 x 359 mm

Voltage rating

12 kV

Fuse type

OHGM



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia