

**ZM140** **Precision locknut**

Precision locknut ZM, accessory ZM..

Technical information**Main Dimensions & Performance Data**

d	M140X2	Thread
D	180 mm	Outside diameter
h	26 mm	Height
M _A	38 Nm	Mounting torque set screw
F _{aB}	690,000 N	Breaking load, axial
M _L	800 Nm	Breakawag
M _{AL}	600 Nm	Mounting torque reference
M _M	133 kg*cm ²	Mass moment of inertia
≈m	1.85 kg	Weight

Dimensions

d ₁	160 mm	Plant diameter outside
t	6 mm	Hight retaining slot
b	14 mm	Width retaining slot
c	13 mm	Distance bore
m	M12	Threaded - threaded pin