



Technical data

NATV10XLL/3AS

Roller follower with inner ring

PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	10 mm
D - External diameter	30 mm
C - Width of bearing, drawn cup or outer ring	14 mm
F - Under roller diameter	15 mm
B - Bearing/Inner ring width	15 mm
e - Inlet diameter of roller or washer	23 mm
Bearing with/without cage	Sans
Radial clearance class	CN
Precision class	P0
Mass	0,065 kg

PRODUCT PERFORMANCE

Cr - Dynamic load rating	12000000 mN
C0r - Static load rating	20300000 mN
Track load capacity cylindrical outer ring	7700000 mN
N lim - Grease lubrication limit speed	39000 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	373,15 °K



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15