



DCS391M2

18V XR Li-Ion Circular Saw

Selling Proposition

- Latest generation 18V XR Li-Ion premium Circular Saw featuring NEW XR 4.0Ah Li-Ion battery technology
- Part of the intelligent XR Lithium Ion Series designed for efficiency and making applications faster
- Powerful & Highly Efficient PM58 DEWALT fan cooled motor with replaceable brushes delivers up to 3700 rotation per minute for fast cutting action
- Ergonomic handle set with rubber overmold to optimise end user comfort
- Extremely durable tool design, including a cast magnesium base for repetitive, accurate cuts
- Intelligent trigger allowing total control over all applications

Standard Equipment

- 165 mm carbide blade
- Hex Key
- Dust Port
- Multi-voltage charger
- 2 slide batteries

Warranty Specifications

- 3 Year Limited Warranty
- 30 Day No Risk Satisfaction Guarantee
- 1 Year Free Service Contract

Specifications	
Voltage	18 V
Battery Capacity	Li-Ion 4.0 Ah
Blade Diameter	165 x 20 mm
Power Output	460 Watts
No Load Speed	3700 rpm
Bevel Capacity	50 °
Max. Depth of Cut at 90°	55 mm
Max. Depth of Cut at 45°	42.1 mm