

FEATURES

- 50 Ω impedance
- Operating frequency is 18GHz

RS PRO straight cable mount SMA connector

RS Stock No.: 217-7776



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO straight cable mount SMA connector features a gold plated body with beryllium copper contact.

This female connector is suitable for use with semi-rigid and flexible cables. It is designed to provide high frequency performance at high power ratings in small diameters.

General Specifications

Type of coaxial connector	Coaxial connector
Body Plating	Gold
Termination method	Solder
Gender	Female
Mounting type	Flange Mount

Electrical Specifications

Temperature Range	-65°~+165°
Characteristic Impedance	50Ω
Frequency Range	0~18GHz
Working Voltage	500V
Insulation Resistance	≥1000MΩ
Medium Pressure	1000V(rms)
VSWR	≤1.23
Working Life	500Cycles

Approvals

Declarations	CE
Hazardous Area Certification	
Standards Met	ROHS

Similar Products

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3
5463181	RS PRO	Coaxial connector	50Ω impedance	Operating frequency is 18GHz	

