



54V XR FLEXVOLT Rail Compatible Circular Saw (190 mm) (2 X 6 Ah)

DCS579T2-QW

54V FLEXVOLT system giving corded performance
DEWALT Brushless Motor for power, extended run-time, reliability & durability

General purpose ripping, crosscutting and bevelling circular saw for wood and other construction materials

Variable adjustment of the bevel angle to 57 degrees

Optimum balance for safe, fatigue-free operation



Sound Pressure Uncertainty	3 dB(A)
----------------------------	---------

Sound Pressure	90 dB(A)
----------------	----------

Uncertainty K 1 (Vibration)	1.5 m/s ²
-----------------------------	----------------------

Battery Capacity	6 Ah
------------------	------

Power Source	Cordless
--------------	----------

No Load Speed	5800 Rpm
---------------	----------