



MASTER TL5 High Output

MASTER TL5 HO 24W/830 1SL

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Product data

• General Characteristics

System Description	High Output
Cap-Base	G5
Cap-Base Information	Green Plate
Bulb	T5 [16 mm]
Life to 10% fail	21000 hr
Preheat EL,3h	
Life to 50% fail	30000 hr
Preheat EL,3h	
LSF HF Preheat	99 %
2000h Rated,3h	
LSF HF Preheat	99 %
4000h Rated,3h	
LSF HF Preheat	99 %
6000h Rated,3h	
LSF HF Preheat	99 %
8000h Rated,3h	
LSF HF Preheat	99 %
12000h Rated,3h	
LSF HF Preheat	97 %
16000h Rated,3h	
LSF HF Preheat	84 %
20000h Rated,3h	

Lum Efficacy Rated	76 Lm/W
HF 25°C	
Lum Efficacy Rated	87 Lm/W
HF 35°C	
LLMF HF 2000h	96 %
Rated	
LLMF HF 4000h	95 %
Rated	
LLMF HF 6000h	94 %
Rated	
LLMF HF 8000h	93 %
Rated	
LLMF HF 12000h	92 %
Rated	
LLMF HF 16000h	91 %
Rated	
LLMF HF 20000h	90 %
Rated	
Design Temperature	35 C
Chromaticity Coordinate X	440 -
Chromaticity Coordinate Y	403 -

• Light Technical Characteristics

Colour Code	830 [CCT of 3000K]
Colour Rendering Index	80 (min), 82 (nom), 85 (max) Ra8
Colour Designation	Warm white
Colour Temperature	3000 K
Luminous Flux EL	1700 Lm
25°C, Rated	
Luminous Flux EL	1700 Lm
25°C, Nominal	
Luminous Flux Lamp	1950 Lm
EL 35°C	

• Electrical Characteristics

Lamp Wattage	24 W
Lamp Wattage EL	22.5 W
25°C, Rated	
Lamp Wattage EL	24.0 W
25°C, Nominal	
Lamp Wattage EL	22.5 W
35°C	
Lamp Voltage EL	77 V
25°C	
Lamp Voltage EL	75 V
35°C	



MASTER TL5 High Output

Lamp Current EL 25°C 0.295 A
 Lamp Current EL 35°C 0.300 A
 Dimmable yes

Insertion Length B 553.7 (min), 556.1 (max) mm
 Overall Length C 563.2 (max) mm
 Diameter D 17 (max) mm

• Environmental Characteristics

Energy Efficiency Label (EEL) A
 Mercury (Hg) Content 1.4 mg
 Energy consumption kWh/1000h 25 kWh

• Measuring Conditions

Calibration Current 0.300 A
 HF Generator Rated Voltage 150 V
 Resistor 250 ohm


• Product Dimensions

Base Face to Base Face A 549.0 (max) mm

• Product Data


Order code 639585 55
 Full product code 871150063958555
 Full product name MASTER TL5 HO 24W/830 1SL
 Order product name MASTER TL5 HO 24W/830 1SL/40
 Pieces per pack 1
 Packing configuration 40
 Packs per outerbox 40
 Bar code on pack - EAN1 8711500639585
 Bar code on outerbox - EAN3 8711500867759
 Logistic code(s) - 12NC 927928083055
 ILCOS code FDH-24/30/1B-L/P-G5-16/550
 Net weight per piece 54.000 gr

Dimensional drawing





MASTER TL5 HO 24W/830 1SL

Product	A (Max)	B (Min)	B (Max)	C (Max)	D (Max)
TL5 HO 24W/830	549.0	553.7	556.1	563.2	17



G5

Photometric data



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, October 31
data subject to change