



PRODUCT-DETAILS

UA1-110

UA1-110 Undervoltage release 110V 110V
50Hz/120V 60Hz



概要信息	
产品型号	UA1-110
产品ID	1SAM201904R1004
欧洲商品编号(EAN)	4013614320453
目录说明	UA1-110 Undervoltage release 110V 110V 50Hz/120V 60Hz
详细描述	Undervoltage release UA1 releases the manual motor starter or prevents it from being switched on when its voltage supply is interrupted. This can be used in emergency switching circuits or can prevent an automatic restart after voltage interruption. UA1 is attached laterally on the left side of MS116, MS132 or MS165 manual motor starters.

订货信息	
最小起订量	1 piece
海关关税号	85365080

Popular Downloads	
数据手册, 技术资料	1SBC100214C0202
说明书和手册	2CDC131011M6802

	2CDC131034M6801
	2CDC131022M6802
	2CDC131120M6801
	2CDC131081M6801
	2CDC131082M6801
说明书和手册（第3部分）	1SBC100214C0202
CAD Dimensional Drawing	2CDC001079B0201

尺寸

产品净宽	18 mm
产品净高	90 mm
产品净深	75.5 mm
产品净重	0.1 kg

技术参数

端子类型	Screw Terminals
额定控制供电电压 (U _s)	(50 Hz) 110 V (60 Hz) 120 V
额定冲击耐受电压 (U _{imp})	Auxiliary Circuit 6 kV
额定绝缘电压 (U _i)	690 V
辅助电路连接容量	Flexible with Ferrule 1/2x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 1x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 2x 0.75 ... 1.5 mm ² Flexible 1/2x 0.75 ... 2.5 mm ² Rigid 1/2x 1 ... 4 mm ²
拧紧力矩	Auxiliary Circuit 0.8 ... 1.2 N·m
剥线长度	Auxiliary Circuit 10 mm
推荐的螺丝刀	Pozidriv 2
标准	CSA 22.2 No. 14 IEC/EN 60947-1 IEC/EN 60947-4-1 UL 508 UL 60947-1 UL 60947-4-1
产品	Undervoltage Release
适用于	MS116 MS132 MO132 MS165 MO165
适用产品系列	Manual Motor Starter
配件组别	Electrical
配件类型	Undervoltage Release
评论	The mechanical and electrical durability of manual motor starters in combination with UA1/AA1 is reduced. Values are provided on request.

UL/CSA适用的技术参数

辅助电路连接容量	Flexible 1/2x 16-12 AWG
UL/CSA	Stranded 1/2x 16-12 AWG
拧紧力矩UL/CSA	Auxiliary Circuit 7 in·lb

环境条件

周围环境温度	Operation -25 ... +60 °C Storage -50 ... +80 °C
抗机械冲击符合IEC 60068-2-27标准	11 ms Pulse 15g

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SAA963005-4502
RoHS信息	1SAA963006-4502
RoHS状态	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	2CMT2023-006539
WEEE B2C / B2B	Business To Business
WEEE 类别	5. Small Equipment (No External Dimension More Than 50 cm)

认证及声明（文件编码）

ABS认证	1SAA963001-0101
BV认证	1SAA963002-0201
cUL 认证	cUL_E137861
符合性声明 - CE	1SAD101100-3411
Declaration of Conformity - UKCA	1SAD201100-3411
DNV GL Certificate	1SAA963001-0304
LR认证	1SAA963001-0502 1SAA918001-0501
RINA认证	1SAA963002-0802
UL认证	UL_E137861

包装信息

1级包装宽度	93 mm
1级包装长度	25 mm
1级包装高度	80 mm
1级包装 总重	0.11 kg
1级包装 EAN	4013614320453
1级包装单元	box 1 piece
2级包装宽度	280 mm
2级包装长度	395 mm
2级包装高度	210 mm
2级包装 总重	9.175 kg
2级包装 EAN	4013614526114
2级包装单元	carton 80 piece

分类

对象分类代码	Q
ETIM 4	EC002498 - Accessories for low-voltage switch technology
ETIM 5	EC001022 - Under voltage coil
ETIM 6	EC001022 - Under voltage coil

ETIM 7	EC001022 - Under voltage coil
ETIM 8	EC001022 - Under voltage coil
e级	V11.0 : 27370417
UNSPSC	39121010
IDEA 粒度分类代码 (IGCC)	4148 >> Under voltage coil
E-Number (Norway)	4364288
E-Number (Sweden)	3112027

分类

低压产品及系统 → 控制产品 → 电动机起动器 → 电动机起动器
低压产品及系统 → 断路器类产品 → 电动机起动器

