

### **FEATURES**

- Various maximum temperatures offered in this range of thermocouples.
- Fast response
- welded exposed junction
- Teflon insulated wire for added durability

# RS PRO Type K Thermocouple 10m Length, 1/0.2mm Diameter → +260°C

RS Stock No.: 123-6307



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Thermocouples



#### **Product Description**

From RS PRO, comes a range of high quality type K, type J, type N and type T exposed junction thermocouples. Manufactured to high standards, these great value thermocouples are a fantastic solution for temperature measurement and are ideal for test & development.

### **General Specifications**

Thermocouple Type	Type K
Temperature Measurement Range	-75°C to +260°C
Construction	Teflon PTFE insulated twin-twisted lead
Application	Medical, Vehicle diagnostics, Temperature readings in boilers, heating sensors, and ovens, Food thermometers, industrial probes, and sensors

#### **Mechanical Specifications**

Probe Diameter	1/0.2mm
Probe Length	10m
Termination Type	Miniature Plug
Compensating Cable Length	10m
Weight	4KG

### **Approvals**

Compliance/Certifications	IEC 584, IEC 584-3
Standards Met	IEC,ANSI





T/C Type	Conductors	Length	Termination	+Positive tail wire	-Negative tail wire code	Allied Code	RS order Code
'K'	1/0.2mm	1 metre	Mini plug	Green	White	70643600	363-0250
'K'	1/0.2mm	2 metre	Mini plug	Green	White		110-4482
'K'	1/0.2mm	5 metre	Mini plug	Green	White		123-6306
'K'	1/0.2mm	10 metre	Mini plug	Green	White		123-6307
'J'	1/0.2mm	1 metre	Mini plug	Black	White	70643599	363-0244
T'	1/0.2mm	2 metre	Mini plug	Black	White		123-6308
'J'	1/0.2mm	5 metre	Mini plug	Black	White		123-6309
'J'	1/0.2mm	10 metre	Mini plug	Black	White		123-6310
'T'	1/0.2mm	1 metre	Mini plug	Brown	White	70643601	363-0266
'T'	1/0.2mm	2 metre	Mini plug	Brown	White		123-6311
'T'	1/0.2mm	5 metre	Mini plug	Brown	White		123-6312
'T'	1/0.2mm	10 metre	Mini plug	Brown	White		123-6313



T/C Type	Conductors	Cores	Reel Length	Allied code	RS order code
J	1/0.2mm	+Black/-White	25 metres	70657194	827-5980
J	1/0.2mm	+Black/-White	50 metres	70657195	827-5984
J	1/0.315mm	+Black/-White	25 metres	70657198	827-5993
J	1/0.315mm	+Black/-White	50 metres	70657199	827-5996
K	1/0.315mm	+Green/-White	25 metres	70657200	827-6000
K	1/0.315mm	+Green/-White	50 metres	70657205	827-6019
Т	1/0.315mm	+Brown/-White	25 metres	70657208	827-6028
Т	1/0.315mm	+Brown/-White	50 metres	70657206	827-6022
J	1/0.508mm	+Black/-White	25 metres	70657197	827-5990
J	1/0.508mm	+Black/-White	50 metres	70657201	827-6003
K	1/0.508mm	+Green/-White	25 metres	70657203	827-6012
K	1/0.508mm	+Green/-White	50 metres	70657204	827-6016
J	7/0.2mm	+Black/-White	25 metres	70657202	827-6006
K	7/0.2mm	+Green/-White	25 metres	70657207	827-6025
Т	7/0.2mm	+Brown/-White	25 metres	70657209	827-6031
N	7/0.2mm	+Pink/-White	25 metres	70657210	827-6034

	Conductors	Cores	Jacket	Reel Length	Allied Code	RS order code
Exten	sion:					
KX	7/0.2mm	+Green/-White	Green	10 metres	70657084	827-5615
KX	7/0.2mm	+Green/-White	Green	25 metres	70641729	236-3820
KX	7/0.2mm	+Green/-White	Green	50 metres	70657085	827-5619
KX	7/0.2mm	+Green/-White	Green	100 metres	70646156	611-7889
KX	7/0.2mm	+Green/-White	Green	200 metres	70657088	827-5628
JX	7/0.2mm	+Black/-White	Black	10 metres	70641640	219-4753
JX	7/0.2mm	+Black/-White	Black	25 metres	70657078	827-5592
JX	7/0.2mm	+Black/-White	Black	50 metres	70657079	827-5596
JX	7/0.2mm	+Black/-White	Black	100 metres	70641737	236-3915
JX	7/0.2mm	+Black/-White	Black	200 metres	70657081	827-5606
TX	7/0.2mm	+Brown/-White	Brown	10 metres	70641637	219-4703
TX	7/0.2mm	+Brown/-White	Brown	25 metres	70641734	236-3870
TX	7/0.2mm	+Brown/-White	Brown	50 metres	70657095	827-5653
TX	7/0.2mm	+Brown/-White	Brown	100 metres	70651749	762-1146
TX	7/0.2mm	+Brown/-White	Brown	200 metres	70657098	827-5662
NX	7/0.2mm	+Pink/-White	Pink	10 metres	70641635	219-4668
NX	7/0.2mm	+Pink/-White	Pink	25 metres	70657091	827-5637
NX	7/0.2mm	+Pink/-White	Pink	50 metres	70657089	827-5631
NX	7/0.2mm	+Pink/-White	Pink	100 metres	70657092	827-5640
	•					

# Thermocouples



	Conductors	Cores	Jacket	Reel Length	Allied Code	RS order code
Compensating:						
VX (KCB)	7/0.2mm	+Green/-White	Green	10 metres	70657082	827-5609
VX (KCB)	7/0.2mm	+Green/-White	Green	25 metres	70641629	219-4551
VX (KCB)	7/0.2mm	+Green/-White	Green	50 metres	70657080	827-5603
VX (KCB)	7/0.2mm	+Green/-White	Green	100 metres	70641630	219-4573
VX (KCB)	7/0.2mm	+Green/-White	Green	200 metres	70657083	827-5612
VX (KCB)	13/0.2mm	+Green/-White	Green	10 metres	70657086	827-5621
VX (KCB)	13/0.2mm	+Green/-White	Green	25 metres	70657087	827-5625
VX (KCB)	13/0.2mm	+Green/-White	Green	50 metres	70657090	827-5634
VX (KCB)	13/0.2mm	+Green/-White	Green	100 metres	70651750	762-1152
U (RCA)	7/0.2mm	+Orange/-White	Orange	10 metres	70657096	827-5656
U (RCA)	7/0.2mm	+Orange/-White	Orange	25 metres	70646158	611-7902
U (RCA)	7/0.2mm	+Orange/-White	Orange	50 metres	70657097	827-5659
U (RCA)	13/0.2mm	+Orange/-White	Orange	10 metres	70641641	219-4769
U (RCA)	13/0.2mm	+Orange/-White	Orange	25 metres	70657093	827-5643
U (RCA)	13/0.2mm	+Orange/-White	Orange	50 metres	70657094	827-5647
. ,	-		•			

T/C Type KX KX	Conductors 1/0.2mm 1/0.2mm	Cores +Yellow/-Red +Yellow/-Red	Reel Length 25 metres 50 metres	Allied code 70656106 70656111	RS order code 814-0030 814-0049
KX	1/0.2mm	+Yellow/-Red	100 metres	70656109	814-0042
KX KX	7/0.2mm 7/0.2mm	+Yellow/-Red +Yellow/-Red	25 metres 50 metres	70656110 70656113	814-0046 814-0055
KX	7/0.2mm	+Yellow/-Red	100 metres	70656114	814-0058
KX	1/0.3mm	+Yellow/-Red	25 metres	70656104	814-0024
KX	1/0.3mm	+Yellow/-Red	50 metres	70656107	814-0033
KX	1/0.3mm	+Yellow/-Red	100 metres	70656108	814-0036
TX	1/0.3mm	+Blue/-Red	25 metres	70656121	814-0080
TX	1/0.3mm	+Blue/-Red	50 metres	70656126	814-0099
TX	1/0.3mm	+Blue/-Red	100 metres	70656124	814-0092
TX	1/0.2mm	+Blue/-Red	25 metres	70656125	814-0096
TX	1/0.2mm	+Blue/-Red	50 metres	70656128	814-0106
TX	1/0.2mm	+Blue/-Red	100 metres	70656129	814-0109

# Thermocouples



T/C Type	Conductors	Cores	Jacket	Reel Length	Allied code	RS order code	
Extension:							
KX	7/0.2mm	+Yellow/-Red	Yellow	25 m	70656102	814-0018	
KX	7/0.2mm	+Yellow/-Red	Yellow	100 m	70656105	814-0027	
KX	7/0.2mm	+Yellow/-Red	Yellow	200 m	70656103	814-0020	
JX	7/0.2mm	+ White/-Red	Black	25 m	70656096	813-9995	
JX	7/0.2mm	+ White/-Red	Black	100 m	70656098	814-0005	
JX	7/0.2mm	+ White/-Red	Black	200 m	70656099	814-0008	
TX	7/0.2mm	+Blue/-Red	Blue	25 m	70656119	814-0074	
TX	7/0.2mm	+Blue/-Red	Blue	100 m	70656122	814-0083	
TX	7/0.2mm	+Blue/-Red	Blue	200 m	70656123	814-0086	
Compensating:							
VX (KCB)	7/0.2mm	+Yellow/-Red	Yellow	25 m	70656127	814-0103	
VX (KCB)	7/0.2mm	+Yellow/-Red	Yellow	100 m	70656130	814-0112	
VX (KCB)	7/0.2mm	+Yellow/-Red	Yellow	200 m	70656131	814-0115	