

FOKY2.E191581 - ELECTROMAGNETIC INTERFERENCE FILTERS - COMPONENT

Electromagnetic Interference Filters - Component

See General Information for Electromagnetic Interference Filters - Component

ALPHA 3 MANUFACTURING LTD

E191581

DELTRON EMCON HOUSE

HARGREAVES WAY, SAWCLIFFE IND PARK

SCUNTHORPE, N LINCOLNSHIRE DN15 8RF UNITED KINGDOM

Appliance filters, Model(s) *KMF3100R, KMF325R, KMF350R*

Appliance filters, Model(s) *Model No. RES1, followed by F05, -F08, -T05, or -T08, Model No. RES1, followed by -F10, -F15, -T10, or T-15, Model No. RES1, followed by -F20 or -T20; RES1, followed by -F10, -F15, -T10, or T-15; RES1, followed by -F20 or -T20*

Appliance filters, Model(s) *Model No. RID followed by, 01, 02, 03, L03, 06, 08, 10, 15, N01, N02, N03, N06, N08, N10 or N15; followed by 2, 3, 4, 6, A, or B; followed by 0, 1, 2, 3, C, D, E, F, G, J, K, M, R, U, V, X, or Y; followed by S, or H*

Appliance filters, Model(s) *Model No. RIP; followed by -02, -04, or -06; followed by 12, 13, 22, 23, 42, or 43; followed by H0, H1, or H2; may be followed by A*

Appliance filters, Model(s) *Model No. RIQ; followed by -02, -04, or -06; followed by 12, 13, 22, 23, 42, or 43; followed by H0, H1, or H2; may be followed by A*

Appliance filters, Model(s) *Model No. RIS; followed by 02, 04, or 06; followed by 1, or 2; followed by 0, C, D, 2, or 3; followed by H0, H1, H2, or H3; may be followed by A*

Appliance filters, Model(s) *Model RIH followed by, 01, 02, 03, L03, 06, 08, 10, 15, N01, N02, N03, N06, N08, N10 or N15; followed by 2, 3, 4, 6, A, or B; followed by 0, 1, 2, 3, C, D, E, F, G, J, K, M, R, U, V, X, or Y; followed by S, or H*

Appliance filters, Model(s) *Model RIX followed by 01, 02, 03, 06, N01, N02, N03, N06 or L03, followed by 2, 4, A, or B followed by 1, 2, 3, O0, C, D, or E followed by S, P, or H*

Appliance filters, Model(s) *RES10F01, RES10F01-L, RES10F01-M, RES10F03, RES10F03-L, RES10F03-M, RES10F06, RES10F06-L, RES10F06-M, RES10F10, RES10F10-L, RES10F10-M, RES10F12, RES10F12-L, RES10F12-M, RES10F13, RES10F13-L, RES10F13-M, RES10F20, RES10F20-L, RES10F20-M, RES10S20, RES10S20-L, RES10S20-M, RES10S30, RES10S30-L, RES10S30-M, RES10S60, RES10S60-L, RES10S60-M, RES10W01, RES10W01-L, RES10W01-M, RES10W03, RES10W03-L, RES10W03-M, RES10W06, RES10W06-L, RES10W06-M, RES10W10, RES10W10-L, RES10W10-M, RES10W12, RES10W12-L, RES10W12-M, RES10W13, RES10W13-L, RES10W13-M, RES10W16-L, RES10W16-M, RES10W20, RES10W20-L, RES10W20-M, RES20F01, RES20F01-L, RES20F01-M, RES20F03, RES20F03-L, RES20F03-M, RES20F06, RES20F06-L, RES20F06-M, RES20F10, RES20F10-L, RES20F10-M, RES20F12, RES20F12-L, RES20F12-M, RES20F16, RES20F16-L, RES20F16-M, RES20F20, RES20F20-L, RES20F20-M, RES20S20, RES20S20-L, RES20S20-M, RES20S30, RES20S30-L, RES20S30-M, RES20S60, RES20S60-L, RES20S60-M, RES20W01, RES20W01-L, RES20W01-M, RES20W03, RES20W03-L, RES20W03-M, RES20W06, RES20W06-L, RES20W06-M, RES20W10, RES20W10-L, RES20W10-M, RES20W12, RES20W12-L, RES20W12-M, RES20W16, RES20W16-L, RES20W16-M, RES20W20, RES20W20-L, RES20W20-M*

Appliance filters, Model(s) *RES3 followed by F or T, followed by 03, 05, followed by 14, 17*

Appliance filters, Model(s) *RES30F01, RES30F01-L, RES30F01-M, RES30F03, RES30F03-L, RES30F03-M, RES30F04, RES30F04-L, RES30F04-M, RES30F06, RES30F06-L, RES30F06-M, RES30F08, RES30F08-L, RES30F08-M, RES30F10, RES30F10-L, RES30F10-M, RES30F12, RES30F12-L, RES30F12-M, RES30F16, RES30F16-L, RES30F16-M, RES30F20, RES30F20-L, RES30F20-M, RES30S20, RES30S20-L, RES30S20-M, RES30S30, RES30S30-L, RES30S30-M, RES30W01, RES30W01-L, RES30W01-M, RES30W03, RES30W03-L, RES30W03-M, RES30W04, RES30W04-L, RES30W04-M, RES30W06, RES30W06-L, RES30W06-M, RES30W08, RES30W08-L, RES30W08-M, RES30W10, RES30W10-L, RES30W10-M, RES30W12, RES30W12-L, RES30W12-M, RES30W16, RES30W16-L, RES30W16-M, RES30W20, RES30W20-L, RES30W20-M*

Appliance filters, Model(s) RES5 followed by F or T, followed by 03, 05, 08, 10, 15

Appliance filters, Model(s) RES60F01, RES60F01-L, RES60F01-M, RES60F03, RES60F03-L, RES60F03-M, RES60F06, RES60F06-L, RES60F06-M, RES60F10, RES60F10-L, RES60F10-M, RES60F12, RES60F12-L, RES60F12-M, RES60F16, RES60F16-L, RES60F16-M, RES60F20, RES60F20-L, RES60F20-M, RES60S20, RES60S20-L, RES60S20-M, RES60S30, RES60S30-L, RES60S30-M, RES60W01, RES60W01-L, RES60W01-M, RES60W03, RES60W03-L, RES60W03-M, RES60W06, RES60W06-L, RES60W06-M, RES60W10, RES60W10-L, RES60W10-M, RES60W12, RES60W12-L, RES60W12-M, RES60W16, RES60W16-L, RES60W16-M, RES60W20, RES60W20-L, RES60W20-M, RES70F01, RES70F01-L, RES70F01-M, RES70F03, RES70F03-L, RES70F03-M, RES70F06, RES70F06-L, RES70F06-M, RES70F10, RES70F10-L, RES70F10-M, RES70F12, RES70F12-L, RES70F12-M, RES70F16, RES70F16-L, RES70F16-M, RES70S25, RES70S25-L, RES70S25-M, RES70S36, RES70S36-L, RES70S36-M, RES70W01, RES70W01-L, RES70W01-M, RES70W03, RES70W03-L, RES70W03-M, RES70W06, RES70W06-L, RES70W06-M, RES70W10, RES70W10-L, RES70W10-M, RES70W12, RES70W12-L, RES70W12-M, RES70W16, RES70W16-L, RES70W16-M, RES80F01, RES80F01-L, RES80F01-M, RES80F03, RES80F03-L, RES80F03-M, RES80F06, RES80F06-L, RES80F06-M, RES80F10, RES80F10-L, RES80F10-M, RES80F12, RES80F12-L, RES80F12-M, RES80F16, RES80F16-L, RES80F16-M, RES80W01, RES80W01-L, RES80W01-M, RES80W03, RES80W03-L, RES80W03-M, RES80W06, RES80W06-L, RES80W06-M, RES80W10, RES80W10-L, RES80W10-M, RES80W12, RES80W12-L, RES80W12-M, RES80W16, RES80W16-L, RES80W16-M, RES90F01, RES90F01-L, RES90F01-M, RES90F03, RES90F03-L, RES90F03-M, RES90F04, RES90F04-L, RES90F04-M, RES90F06, RES90F06-L, RES90F06-M, RES90F08, RES90F08-L, RES90F08-M, RES90F10, RES90F10-L, RES90F10-M, RES90F12, RES90F12-L, RES90F12-M, RES90F16, RES90F16-L, RES90F16-M, RES90F20, RES90F20-L, RES90F20-M, RES90S20, RES90S20-L, RES90S20-M, RES90S30, RES90S30-L, RES90S30-M, RES90W01, RES90W01-L, RES90W01-M, RES90W03, RES90W03-L, RES90W03-M, RES90W04, RES90W04-L, RES90W04-M, RES90W06, RES90W06-L, RES90W06-M, RES90W08, RES90W08-L, RES90W08-M, RES90W10, RES90W10-L, RES90W10-M, RES90W12, RES90W12-L, RES90W12-M, RES90W16, RES90W16-L, RES90W16-M, RES90W20, RES90W20-L, RES90W20-M, RIDN03B3H-WOG, RIDN03B3H-WP

Appliance filters, Model(s) RIR followed by -02, -04, or -06, followed by I or 2, followed by 1, 2, 3, 0, C, D, E, F, G, J, K, M, R, U, V, X or Y followed by the letter -H or -S, followed with or without the letter N, followed with or without the letter A.

Appliance filters, Model(s) RIR2, followed by N or blank, followed by 02, 04 or 06, followed by 2, 3, 4, 6, A, B, C or D, followed O, C, D, G, F, E, 1, 2 or 3, followed by S or H.

Appliance filters, Model(s) RIR3 (a)

Electromagnetic Interference Filter ? Appliance, Model(s) KMF3180AX

Electromagnetic interference filters, Model(s) 301002015, 301002021, D37370030, KMF1320A, KMF306, KMF306A, KMF306V, KMF310, KMF3100, KMF3100A, KMF3100LC, KMF3100V, KMF310A, KMF310AX, KMF310V, KMF3150, KMF3150A, KMF3150LC, KMF3150V, KMF318, KMF3180, KMF3180A, KMF3180V, KMF318A, KMF318V, KMF325, KMF325A, KMF325AX, KMF325V, KMF3320A, KMF3320T, KMF3320V, KMF336, KMF336A, KMF336LC, KMF336V, KMF3420A, KMF3420V, KMF3420VX, KMF350, KMF350A, KMF350LC, KMF350V, KMF350X, KMF3620A, KMF3620V, KMF3620VX, KMF370, KMF370A, KMF370LC, KMF370V, KMF3820A, KMF3820V, KMF4320A, MDF06, MDF16, MDF16WOC, MDF18, MDF25, MDF308, MDF3100, MDF3150, MDF318, MDF325, MDF336, MDF350, MDF36, MDF370, MDF50, MIF03, MIF06, MIF10, MIF16, MIF23, MIF306, MIF310, MIF3100, MIF3150, MIF316, MIF3180, MIF323, MIF323, MIF330, MIF330B, MIF3400, MIF3400B, MIF350, MIF350B, MIF375, MIF375B, MIF3800, SF1591, SF1598, SF1633, SF1637, SF1638, SF1639, SF1639B, SF1641, SF1641B, SF1644, SF1645, SF1648, SF1649, SF1655, SF1656, SF1657, SF1658

(a) - Followed by -N or blank, followed by 03, 06, or 10, followed by 2, 3, 4, 6, A, B, C or D, followed by O, C, D, E, G, F, 1, 2 or 3, followed by S or H

Marking: Company name or trademark  and model designation.

Last Updated on 2018-11-21

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2019 UL LLC"

FOKY8.E191581 - ELECTROMAGNETIC INTERFERENCE FILTERS CERTIFIED FOR CANADA - COMPONENT

Electromagnetic Interference Filters Certified for Canada - Component

See General Information for Electromagnetic Interference Filters Certified for Canada - Component

ALPHA 3 MANUFACTURING LTD

E191581

DELTRON EMCON HOUSE

HARGREAVES WAY, SAWCLIFFE IND PARK

SCUNTHORPE, N LINCOLNSHIRE DN15 8RF UNITED KINGDOM

Appliance filters, Model(s) KMF3100R, KMF325R, KMF350R, RES10F01, RES10F01-L, RES10F01-M, RES10F03, RES10F03-L, RES10F03-M, RES10F06, RES10F06-L, RES10F06-M, RES10F10, RES10F10-L, RES10F10-M, RES10F12, RES10F12-L, RES10F12-M, RES10F13, RES10F13-L, RES10F13-M, RES10F20, RES10F20-L, RES10F20-M, RES10S20, RES10S20-L, RES10S20-M, RES10S30, RES10S30-L, RES10S30-M, RES10S60, RES10S60-L, RES10S60-M, RES10W01, RES10W01-L, RES10W01-M, RES10W03, RES10W03-L, RES10W03-M, RES10W06, RES10W06-L, RES10W06-M, RES10W10, RES10W10-L, RES10W10-M, RES10W12, RES10W12-L, RES10W12-M, RES10W13, RES10W13-L, RES10W13-M, RES10W16-L, RES10W16-M, RES10W20, RES10W20-L, RES10W20-M, RES20F01, RES20F01-L, RES20F01-M, RES20F03, RES20F03-L, RES20F03-M, RES20F06, RES20F06-L, RES20F06-M, RES20F10, RES20F10-L, RES20F10-M, RES20F12, RES20F12-L, RES20F12-M, RES20F16, RES20F16-L, RES20F16-M, RES20F20, RES20F20-L, RES20F20-M, RES20S20, RES20S20-L, RES20S20-M, RES20S30, RES20S30-L, RES20S30-M, RES20S60, RES20S60-L, RES20S60-M, RES20W01, RES20W01-L, RES20W01-M, RES20W03, RES20W03-L, RES20W03-M, RES20W06, RES20W06-L, RES20W06-M, RES20W10, RES20W10-L, RES20W10-M, RES20W12, RES20W12-L, RES20W12-M, RES20W16, RES20W16-L, RES20W16-M, RES20W20, RES20W20-L, RES20W20-M, RES30F01, RES30F01-L, RES30F01-M, RES30F03, RES30F03-L, RES30F03-M, RES30F04, RES30F04-L, RES30F04-M, RES30F06, RES30F06-L, RES30F06-M, RES30F08, RES30F08-L, RES30F08-M, RES30F10, RES30F10-L, RES30F10-M, RES30F12, RES30F12-L, RES30F12-M, RES30F16, RES30F16-L, RES30F16-M, RES30F20, RES30F20-L, RES30F20-M, RES30S20, RES30S20-L, RES30S20-M, RES30S30, RES30S30-L, RES30S30-M, RES30W01, RES30W01-L, RES30W01-M, RES30W03, RES30W03-L, RES30W03-M, RES30W04, RES30W04-L, RES30W04-M, RES30W06, RES30W06-L, RES30W06-M, RES30W08, RES30W08-L, RES30W08-M, RES30W10, RES30W10-L, RES30W10-M, RES30W12, RES30W12-L, RES30W12-M, RES30W16, RES30W16-L, RES30W16-M, RES30W20, RES30W20-L, RES30W20-M, RES60F01, RES60F01-L, RES60F01-M, RES60F03, RES60F03-L, RES60F03-M, RES60F06, RES60F06-L, RES60F06-M, RES60F10, RES60F10-L, RES60F10-M, RES60F12, RES60F12-L, RES60F12-M, RES60F16, RES60F16-L, RES60F16-M, RES60F20, RES60F20-L, RES60F20-M, RES60S20, RES60S20-L, RES60S20-M, RES60S30, RES60S30-L, RES60S30-M, RES60W01, RES60W01-L, RES60W01-M, RES60W03, RES60W03-L, RES60W03-M, RES60W06, RES60W06-L, RES60W06-M, RES60W10, RES60W10-L, RES60W10-M, RES60W12, RES60W12-L, RES60W12-M, RES60W16, RES60W16-L, RES60W16-M, RES60W20, RES60W20-L, RES60W20-M, RES70F01, RES70F01-L, RES70F01-M, RES70F03, RES70F03-L, RES70F03-M, RES70F06, RES70F06-L, RES70F06-M, RES70F10, RES70F10-L, RES70F10-M, RES70F12, RES70F12-L, RES70F12-M, RES70F16, RES70F16-L, RES70F16-M, RES70S25, RES70S25-L, RES70S25-M, RES70S36, RES70S36-L, RES70S36-M, RES70W01, RES70W01-L, RES70W01-M, RES70W03, RES70W03-L, RES70W03-M, RES70W06, RES70W06-L, RES70W06-M, RES70W10, RES70W10-L, RES70W10-M, RES70W12, RES70W12-L, RES70W12-M, RES70W16, RES70W16-L, RES70W16-M, RES80F01, RES80F01-L, RES80F01-M, RES80F03, RES80F03-L, RES80F03-M, RES80F06, RES80F06-L, RES80F06-M, RES80F10, RES80F10-L, RES80F10-M, RES80F12, RES80F12-L, RES80F12-M, RES80F16, RES80F16-L, RES80F16-M, RES80W01, RES80W01-L, RES80W01-M, RES80W03, RES80W03-L, RES80W03-M, RES80W06, RES80W06-L, RES80W06-M, RES80W10, RES80W10-L, RES80W10-M, RES80W12, RES80W12-L, RES80W12-M, RES80W16, RES80W16-L, RES80W16-M, RES90F01, RES90F01-L, RES90F01-M, RES90F03, RES90F03-L, RES90F03-M, RES90F04, RES90F04-L, RES90F04-M, RES90F06, RES90F06-L, RES90F06-M, RES90F08, RES90F08-L, RES90F08-M, RES90F10, RES90F10-L, RES90F10-M, RES90F12, RES90F12-L, RES90F12-M, RES90F16, RES90F16-L, RES90F16-M, RES90F20, RES90F20-L, RES90F20-M, RES90S20, RES90S20-L, RES90S20-M, RES90S30, RES90S30-L, RES90S30-M, RES90W01, RES90W01-L, RES90W01-M, RES90W03, RES90W03-L,

RES90W03-M, RES90W04, RES90W04-L, RES90W04-M, RES90W06, RES90W06-L, RES90W06-M, RES90W08, RES90W08-L, RES90W08-M, RES90W10, RES90W10-L, RES90W10-M, RES90W12, RES90W12-L, RES90W12-M, RES90W16, RES90W16-L, RES90W16-M, RES90W20, RES90W20-L, RES90W20-M

Electromagnetic Interference Filter ? Appliance, Model(s) KMF3180AX

Electromagnetic interference filters, Model(s) KMF1320A, KMF306, KMF306A, KMF306V, KMF310, KMF3100, KMF3100A, KMF3100LC, KMF3100V, KMF310A, KMF310AX, KMF310V, KMF3150, KMF3150A, KMF3150LC, KMF3150V, KMF318, KMF3180, KMF3180A, KMF3180V, KMF318A, KMF318V, KMF325, KMF325A, KMF325AX, KMF325V, KMF3320A, KMF3320T, KMF3320V, KMF336, KMF336A, KMF336LC, KMF336V, KMF3420A, KMF3420V, KMF350, KMF350A, KMF350LC, KMF350V, KMF350X, KMF3620A, KMF3620V, KMF370, KMF370A, KMF370LC, KMF370V, KMF3820A, KMF3820V, KMF4320A, MDF06, MDF16, MDF16WOC, MDF18, MDF25, MDF308, MDF3100, MDF3150, MDF318, MDF325, MDF336, MDF350, MDF36, MDF370, MDF50, MIF03, MIF06, MIF10, MIF16, MIF23, MIF306, MIF310, MIF3100, MIF3150, MIF316, MIF3180, MIF32, MIF323, MIF330, MIF330B, MIF3400, MIF3400B, MIF350, MIF350B, MIF375, MIF375B, MIF3800

Marking: Company name or trademark  , model designation and the
Recognized Component Mark for Canada, .

Last Updated on 2018-10-03

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions:
1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2019 UL LLC"