

Rittal – The System.

Faster – better – everywhere.

Polycarbonate enclosures PK without knockouts – PK 9514.000

Date : Aug 25, 2015

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Polycarbonate enclosures PK without knockouts – PK 9514.000

erstellt am : 25.08.2015 build on www.rittal.com/uk-en



Product description

Material:	Housing: Fibre-glass reinforced polycarbonate Cover screws: Polyamide Insulating bungs: Polyethylene Cover grey: Fibreglass-reinforced polycarbonate, all-round foamed-in PU seal
------------------	--

Colour:	RAL 7035
----------------	----------

Protection category IP to IEC 60 529:	IP 66
--	-------

Protection category NEMA:	NEMA 4X
--------------------------------------	---------

Supply includes:	Enclosure with cover Cover screws Insulating bungs for wall mounting screws
-------------------------	---

Packs of:	2 pc(s).
------------------	----------

EAN:	4028177139497
-------------	---------------

Customs tariff number:	94037000
-----------------------------------	----------

eCl@ss 5.1:	27180102
--------------------	----------

eCl@ss 7.0:	27180101
--------------------	----------

ETIM 6.0:	EC000261
------------------	----------

Product features	
Dimensions:	Width: 180 mm Height: 110 mm Depth: 90 mm
Cover:	grey
Ambient temperature range:	-35°C...+80°C
Weight/pack:	0.89 kg
Approvals	
Approvals:	 Bureau Veritas (EN)  C-UL (EN)  UL (EN)
Declarations:	 Declaration of conformity (DE)
Downloads	
Data sheets:	 Technical details EN
CAD drawings:	Request