

Datasheet

RS Stock No.9172340

RS Pro Polyurethane Airline with 1/4" BSP Couplings



Designed to overcome the limitations of traditional nylon preformed coil, Polyurethane Compact Coils offer excellent resistance to abrasion, oils and kinking, as well as improved flexibility.

- Preformed with press in swivel couplings complete with springs.
- Excellent resistance to abrasion.
- Very good kink resistant characteristics.
- Complies with current F&DA regulations.
- Useful for confined areas limited by space / bend radius.
- Service Temperature -20°C to + 65°C.
- Maximum working pressure: 10 bar.
- 2m Working length
- 10mm OD
- 12.5 turns
- 500 / 1000mm tail lengths
- 51mm Coil diameter
- Press in 1/4" and 3/8" BSPT press in swivel couplings complete with springs.
- Blue
- Industrial applications using air tools, instrumentation, robotics.