

## FEX FEX 1919 13 T



**Order symbol:** FEX 1919 13 T  
**Product nbr:** 4120800  
**Description:** Enclosure, PC  
**Remarks:** Ex e II, EN 60079; IK 4J

**EAN:** 6418074007865  
**El. number:**  
Finland: 3424636  
Denmark: 8212026311  
Italy: 7801010  
Sweden: 4120800  
Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with silicone gasket and polyamide cover screws.

Sample photo

| Dimensions:            |  | Length               | Width | Height | Rating:                                    |
|------------------------|--|----------------------|-------|--------|--------------------------------------------|
| mm:                    |  | 188                  | 188   | 130    | Ingress Protection (EN 60529): IP 54       |
| inch:                  |  | 7.4                  | 7.4   | 5.1    | Impact Resistance (EN 50014): 4J           |
| Materials:             |  |                      |       |        | Electrical insulation: Totally insulated   |
| Material:              |  | Polycarbonate        |       |        | Halogen free (DIN/VDE 0472, Part 815): Yes |
| Base colour:           |  | RAL 7035             |       |        | Certificates:                              |
| Cover colour:          |  | Clear transparent    |       |        |                                            |
| Cover screws material: |  | Polyamide            |       |        |                                            |
| Cover screws colour:   |  | Grey                 |       |        |                                            |
| Gasket material:       |  | Silicone             |       |        |                                            |
| Temperatures:          |  |                      |       |        | ATEX                                       |
| Short term:            |  | -40 ... 120 °C       |       |        | EC Certificate of Conformity               |
| Continuous:            |  | -10 ... 80 °C        |       |        |                                            |
| Short term:            |  | -40 ... 250 °F       |       |        |                                            |
| Continuous:            |  | 14 ... 175 °F        |       |        |                                            |
| Accessories:           |  |                      |       |        |                                            |
| EKHVT                  |  | Mounting plate       |       |        |                                            |
| EKJVT                  |  | Mounting plate       |       |        |                                            |
| EKMVT                  |  | Mounting plate       |       |        |                                            |
| EKOVT                  |  | Mounting plate       |       |        |                                            |
| EKPVT                  |  | Mounting plate       |       |        |                                            |
| EKTVT                  |  | Mounting plate       |       |        |                                            |
| EKUVT                  |  | Mounting plate       |       |        |                                            |
| EKV 12                 |  | DIN-35 Mounting rail |       |        |                                            |
| EKV 22                 |  | DIN-35 Mounting rail |       |        |                                            |
| EKV 32                 |  | DIN-35 Mounting rail |       |        |                                            |

SOLID 188x188x130-180

