

95 11 165 Cable Shears



- Technical details
- Description
- Applications
- PDF

No.	95 11 165	
EAN	4003773040323	
Tool	burnished	
Handles	plastic coated	
Style	1	
	15	Ø mm
	50	mm ²
AWG	1/0	
	165	mm
	215	g
	215	g

- for cutting copper and aluminium single conductors as well as multiple stranded cables
- not suitable for steel wire and hard drawn copper conductors

- precision ground, hardened blades
- clean and smooth cut without crushing and deformation
- easy cutting with one-hand operation
- guard prevents operators' fingers being pinched
- adjustable bolted joint, self-retaining screw
- High-grade special tool steel, forged, oil-hardened



Cut performed with a Diagonal Cutter: high effort required, inaccurate cut, considerable deforming and crushing of the cable



Cut performed with a Cable Shear: easy, clean cut without any deformation of the cable

technical change and errors excepted