



ENGLISH

Datasheet

146-6834
CT702 PROBE



RS Article No.	Body type	Kind of Cable Tester	Conditions of Cable Tester	Display	Operating way	Battery type
146-6834	Plastic	LAN, TEL, COAX, Wires	PASS, OPEN, SHORT.	LED Indicator	Tact Switch Keypad	Alkaline 9VDC



SPECIFICATIONS:

Display:	LED Indicator
Connector Type:	RJ11/12 Connector
Cable Type:	LAN, TEL, COAX, Bare wire
Error Status:	OPEN, SHORT
Toner/Tracer:	Prober Sound Output (Max: 114dB)
Length for Test:	1-350 meters (3~1200 feet)
Power Source:	9 V dc Battery
Operating Temperature:	0° - 50°C (32° - 122°F)
Storage Temperature:	-10° - 60°- C (14° - 140°- F)
Humidity:	10 % - 90 % non-condensing
Dimension:	230 (L) x 60 (W) x 28 (H) mm
Certification:	CE, RoHS