


## FEATURES

- **DALI2, Push Dimming, PWM:** Offers flexible dimming options to suit various lighting needs
- **4.17 A Driver Current:** Provides sufficient current for high-performance LED systems
- **100 277 V AC Input Voltage:** Compatible with a wide range of AC power sources
- **IP66 Rating:** Ensures protection against dust and water, suitable for outdoor use
- **100 W Maximum Output Power:** Delivers ample power for demanding LED applications
- **Constant Voltage Operation:** Maintains consistent voltage output for stable LED performance

## RS PRO 100W LED Driver, 24V Constant Voltage

RS Stock No: 642-787



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

The RS PRO 100W LED Driver is designed to provide reliable power to LED lighting systems. With a constant voltage output of 24V, it ensures stable and efficient operation for a variety of lighting applications. This LED driver supports multiple dimming operations, making it versatile for different lighting environments.

### General Specifications

Dimming Operation	DALI2, Push Dimming, PWM
Number of Outputs	1
Operating Modes	Constant Voltage
Primary Type	AC
Product Type	LED Driver
Sub Type	Constant Voltage LED Driver

### Electrical Specifications

Driver Current	4.17 A
Input Voltage	100-277 V ac
Input Voltage Type	AC
Maximum Output Power	100 W
Output Voltage	24 V

### Protection Category

IP Rating	IP66
-----------	------

### Approvals

Standards/Approvals	CE, EN55015, EN61000-3-2, EN61000-3-3, EN61000-4-2,3,4,5,6,11, EN61347-1, EN61347-2-13, EN61547, EN62493
---------------------	--