

## Uni-Dicht-Verschraubung Pg 16, 11,5-15,5



Image is for illustration purposes only. Please refer to product description.

Part number	09 00 000 5089
Specification	Uni-Dicht-Verschraubung Pg 16, 11,5-15,5
HARTING eCatalogue	<a href="https://harting.com/09000005089">https://harting.com/09000005089</a>

### Identification

Category	Accessories
Type of accessory	Cable gland

### Technical characteristics

Tightening torque	≤10 Nm (depending on the cable and the seal insert used)
Wrench size	24
Limiting temperature	-40 ... +130 °C
Degree of protection acc. to IEC 60529	IP68
Size	Pg 16
Clamping range	11.5 ... 15.5 mm

### Material properties

Material (cable glands)	Metal
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead 2-(2'-Hydroxy-3'-tert-butyl-5'-methylphenyl)-5-chlorobenzotriazole (UV-326)
California Proposition 65 substances	Yes



**Pushing Performance**  
Since 1945

## Material properties

California Proposition 65 substances	Lead Nickel
--------------------------------------	----------------

## Commercial data

Packaging size	10
Net weight	36.08 g
Country of origin	Germany
European customs tariff number	74122000
GTIN	5713140001701
eCl@ss	27140801 Screwed cable gland (electrical)
ETIM	EC000441
UNSPSC 24.0	39121431