



Product data sheet

Power tools for trade & industry

HWS 810/230

INDUSTRIAL HWS 810/230

For heavy-duty grinding work

The most important data

Permitted sanding disc diameter	230 mm
No-load speed	6,600 rpm
Rated power, output	2,000 W

Part Number 0 602 334 504



Technical data

Technical data

Frequency	200 Hz
Voltage	135 V
Permitted sanding disc diameter	230 mm
No-load speed	6,600 rpm
Rated power, input	2,500 W
Rated power, output	2,000 W
Rated current	13.2 A
Weight as per EPTA	7.8 kg
Toolholder, drive end	M14
Switch version	Safety switch

Product data sheet

Power tools for trade & industry



BOSCH
Invented for life

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

