

**BOSCH**

Invented for life

Power tools for trade & industry

Product data sheet



Laser Measure

GLM 30

Distance measurement – easy, compact, for professionals

The most important data

Measurement range	0,15 – 30 m
Measurement accuracy, typical	+/- 2 mm
Measurement time, typical	< 0.5 s

**Part number:** 0 601 072 570**GBP 66,00***[> More product information](#)** Recommended retail price excluding VAT*

Technical data


Laser diode	635 nm, < 1 mW
Measurement range	0,15 – 30 m
Laser class	2
Measurement accuracy, typical	+/- 2 mm
Measurement time, typical	< 0.5 s
Measurement time, max.	4 s
Power supply	2 x 1.5 V LR03 (AAA)
Automatic deactivation	5 min.
Weight, approx.	0,1 kg
Length	105 mm
Width	41 mm
Height	24 mm
Units of measurement	Metric
Battery lifetime, individual measurements, approx.	5.000
Dust and splash protection	IP 54

**BOSCH**

Invented for life

Power tools for trade & industry**Advantages:**

- One button for everything – intuitive and easy measuring
- Compact – easily fits into any pocket
- Automatically adds together measurements using AutoSum function
- Extremely tough – Dust, splash and impact protected on the jobsite
- ISO-certified laser measure
- Clearly legible readings thanks to illuminated 3-line display

**Prices / Scope of delivery**

Part number	0 601 072 570
2 x 1.5 V LR03 (AAA) batteries	✓
Manufacturer's certificate	✓
Protective bag	✓
Price (Recommended retail price excluding VAT)	GBP 66,00