


TOLERANCES (UNLESS SPECIFIED)	
0-10mm	±0.2mm
10.1-50mm	±0.5mm
50.1-250mm	±1.0mm
>250mm	±2.0mm



PORTABLE TRANSFORMER

TYPE	ISOLATION
INPUT	230V 50Hz
OUTPUT	55-0-55V
	CENTER TAP EARTHED
RATING	3KVA CONTINUOUS
THERMAL CUT-OUT	15A
SOCKET	32A BS EN 60309
	RATED IP44
INPUT	2m LEAD WITH BARE ENDS
ENCLOSURE	MILD STEEL
	RATED IP22
COLOUR	YELLOW

REV	
4	
3	
2	
1	LEAD CORRECTED, GB 2/11/09

CARROLL & MEYNELL
 TRANSFORMERS LIMITED
 TEL: 01642 617406 FAX: 01642 614178
 enquiries@carroll-meynell.com

TITLE	PORTABLE TOOL TRANSFORMER CMHT3
ALL DIMENSIONS IN mm	

DRAWN	PROJECTION	DATE	SCALE
SH		26/4/8	NTS
DRAW No	REV	PAGE	
6059	1	1/1	