

LEDVANCE® Linear Power

Indoor luminaires | LED surface-mounted luminaire



Area of application

- General indoor illumination
- Corridors, entrance lighting
- Accent lighting, public areas
- Cove lighting
- Shelves, furniture integration or under cabinet lighting


Product benefits

- Compact dimensions
- Easy to install in two different mounting angles
- Energy savings of up to 45% compared to conventional linear luminaires
- Complete mounting and connecting accessories included
- Connect up to 10 luminaires in series
- High light output system
- Different lengths available
- For seamless lines of light
- Available certificates: CE, CB, TUEV SUED

Product features

- High luminous efficacy: up to 100 lm/W
- Luminous flux: up to 2500lm
- Available with color temperature: 3000K, 4000K
- Beam angle: 140°
- Type of protection: IP20
- White polycarbonate housing and diffuser
- Ambient operating temperature: -20...+40 °C
- Lifetime (L70/B50): up to 30000h
- 3-years guarantee

Technical data



Product description	GTIN (EAN)	Nominal wattage [W]	Nominal voltage [V]	Power factor [λ]	Luminous flux [lm]	Luminaire efficacy [lm/W]	Colour temperature [K]	CRI index [Ra]
LinearLED 600 Power 10W/3000K IP20	4058075000360	10W	230V	> 0.5	1000	100	3000K	>80
LinearLED 600 Power 10W/4000K IP20	4058075000384	10W	230V	> 0.5	1000	100	4000K	>80
LinearLED 1200 Power 20W/3000K IP20	4058075000407	20W	230V	> 0.5	2000	100	3000K	>80
LinearLED 1200 Power 20W/4000K IP20	4058075000421	20W	230V	> 0.5	2000	100	4000K	>80
LinearLED 1500 Power 25W/3000K IP20	4058075000445	25W	230V	> 0.9	2500	100	3000K	>80
LinearLED 1500 Power 25W/4000K IP20	4058075000469	25W	230V	> 0.9	2500	100	4000K	>80

Product description	Beam angle	Rated life time L70 / B50 [h]	Type of protection IP rating	Protection class	Product size l x w or ø [mm]	Height h [mm]	Body colour
LinearLED 600 Power 10W/3000K IP20	140°	30000	20	II	573 x 28	36	white
LinearLED 600 Power 10W/4000K IP20	140°	30000	20	II	573 x 28	36	white
LinearLED 1200 Power 20W/3000K IP20	140°	30000	20	II	1173 x 28	36	white
LinearLED 1200 Power 20W/4000K IP20	140°	30000	20	II	1173 x 28	36	white
LinearLED 1500 Power 25W/3000K IP20	140°	30000	20	II	1473 x 28	36	white
LinearLED 1500 Power 25W/4000K IP20	140°	30000	20	II	1473 x 28	36	white

Packaging information

Product description	GTIN (EAN)	Dimensions EAN10 l x w x h [mm]	Gross weight EAN 10 [g]	Volume [dm³]	Packaging unit [Pieces/unit]
LinearLED 600 Power 10W/3000K IP20	4058075000360	780 x 40 x 30	385	1.37	25
LinearLED 600 Power 10W/4000K IP20	4058075000384	780 x 40 x 30	385	1.37	25
LinearLED 1200 Power 20W/3000K IP20	4058075000407	1380 x 40 x 30	558	2.38	25
LinearLED 1200 Power 20W/4000K IP20	4058075000421	1380 x 40 x 30	558	2.38	25
LinearLED 1500 Power 25W/3000K IP20	4058075000445	1680 x 40 x 30	780	2.88	25
LinearLED 1500 Power 25W/4000K IP20	4058075000469	1680 x 40 x 30	780	2.88	25

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.