

Datasheet

RS Pro Crimp Tool for Flag Terminals

RS Stock No: 456-7709



Specifications:

- Non slip main handle and low friction moving handle ensure a comfortable hand grip
- Provides two-hand grip in the final phase of crimping, increasing comfort and productivity
- Full cycle crimp mechanism to ensure consistent, reliable crimp
- Ratchet release mechanism to clear mis-crimps and obstructions
- Precision eccentric adjustment for consistent performance and ability to calibrate
- Each tool has a unique serial number for traceability
- Durable: life span exceeds 50,000 cycles
- High strength, through hardened alloy Swedish steel construction

Crimp nest:	0,75-2,5 mm ² / 18-14 AWG
Wire size:	0,75-2,5mm ² / 18-14 AWG
Connector:	6.3 mm flag terminals
Description:	Crimping tool for 6.3 mm flag terminals
Crimp profile:	B/F Open barrel
Length:	225 mm/8,86"
Width:	21 mm/ 0,83"
Height:	70 mm/ 2,76"
Weight:	537 gr/ 1.18 lb
Life span, cycles:	50,000