



Datasheet

Stock No: 440-492

ENGLISH

RS Pro DC Motor Controller, Potentiometer Control, 12 V dc, 24 V dc, 12 A, Box Mount



Product Details

Low Voltage 12/24V

This range of cost effective low voltage dc. motor controllers are suitable for use with permanent magnet dc. motors up to 12A. The boxed version is protected to IP22., Comprehensive instruction sheet supplied.

Adjustable maximum and minimum speeds

IR compensation

Adjustable overload

Fused input supply

Available as boxed (440-492) or unboxed (440-486) versions

Supply either lead acid battery or mains with the addition of suitable transformer, rectifier and smoothing capacitors

Specifications:

Supply Voltage	12 V dc, 24 V dc
Current Rating	12 A
Voltage Rating	24 V dc
Compatible Motor Type	Permanent Magnet, Shunt
Control Input	Potentiometer
Mounting Style	Box