

Thalassa PHD outdoor heavy duty ventilated plinth H200 W750 D420 RAL7035 P55

NSYZZ274VHD

! To be discontinued on: 30 Jun 2025

(!) Discontinued

EAN Code: 3606480680960

Main

Range	Thalassa	
Application	Outdoor heavy duty	
Accessory / separate part category	Enclosure accessory	
Product or component type	Ventilated plinth	
Application	Multi-purpose	
Nominal dimensions of the housing	-	
Device composition	fixing elements 2 front panel 2 side part 1 stainless steel anti-insect filter	
Range compatibility	Thalassa Thalassa PHD	

Complementary

Fixing mode	By screws - on side parts location
Colour	Plinth: grey (RAL 7035)
Height	200 mm
Width	750 mm
Depth	420 mm

Environment

IP degree of protection	IP55 conforming to IEC 60529 (completed plinth with grille and filter)	
IK degree of protection	IK10 conforming to IEC 62262	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.000 cm
Package 1 Width	44.000 cm
Package 1 Length	85.000 cm
Package 1 Weight	7.798 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	20

Package 2 Height	115.000 cm	
Package 2 Width	100.000 cm	
Package 2 Length	120.000 cm	
Package 2 Weight	170.460 ka	

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	1341ad4e-77b9-40e3-bab0-32043fbc5959
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No