



## M18 FUEL 125mm Variable Speed Braking Grinder

M18 FSAGV125XB-0X0

- Generates Corded Power - Powerful POWERSTATE Brushless Motor spins at 8,500 RPM and allows the user to complete the toughest grinding and cutting applications
- Increased Control - Variable speed control for applications that require lower RPM grinding; 3500 - 8500 RPM
- 5 Speed Settings

### MODEL VARIANT



### INCLUDES

- M18 FSAGV125XB (1)
- FIXTEC Nut (1)
- Dynacase (1)
- Safety Guard (1)
- Side Handle (1)

Categories: Grinders



### WHAT'S INCLUDED

M18 FSAGV125XB-0X0

M18 FSAGV125XB (1)

Safety Guard (1)

FIXTEC Nut (1)

Side Handle (1)

Dynacase (1)

### PRODUCT SPECIFICATIONS

|                                             |                          |
|---------------------------------------------|--------------------------|
| Length (mm)                                 | 333.3                    |
| Height (mm)                                 | 111.9                    |
| Battery platform                            | M18 REDLITHIUM-ION       |
| Voltage (V)                                 | 18                       |
| No Load Speed (rpm)                         | 3,500 -8,500 RPM         |
| Disc diameter (mm)                          | 125                      |
| Weight with battery pack if applicable (kg) | 2.7 kg (w/5.0Ah battery) |