



2 YEARS
MANUFACTURER
GUARANTEE



Product number
EAN

1178600800
4007123663408

TECHNICAL DATA

Luminous flux	1250 lm
Colour temperature	7000 K
Colour rendering index	70-79 (class 2 A)
Battery capacity	4 Ah
Battery voltage	3.7 V
Light duration max.	15 h
Battery charging time approx.	4 h

Number of batteries	1
Battery type	26650
Battery technology	Lithium-ion
Impact strength	IK07
Protection class	III
Degree of protection (IP)	IP67
Colour	black

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1
Weight of product (without packaging)	0.34 kg
Dimension LxWxH (without packing)	15.5 cm x 4.3 cm x 4.3 cm

Weight of product (including packaging)	0.45 kg
Dimension LxWxH (incl. packing)	9 cm x 6 cm x 25.5 cm