

## 1100-1.30

### Internal extractor set

in L-BOXX® 136, 8 pieces

Code	ETIM
<b>2836041</b>	<b>EC011834</b>
EAN	UNSPSC
<b>4010886939413</b>	<b>27-11-17-12</b>
Country of origin	eCl@ss
<b>Germany</b>	<b>21-04-90-90</b>
Customs tariff number	
<b>82055980</b>	



### Article description

- For inner diameter 12 - 35 mm
- For extremely-tightly-packed ball bearings, bearing races, bushings, and shaft seals Simmering®
- With slide hammer and counter support
- No. 1100 CT2-1.04/12A for retrofitting existing L-BOXX®s 136
- With Check-Tool insert for quick check of tool completeness
- As tools are fully sunk in the foam, the equipped insert can be stacked
- Insert can be used in drawers with minimum dimensions 400 x 310 x 90 mm

### Article parts list

Internal extractor No. 1.30/2.12-15 mm, Internal extractor No. 1.30/3.15-19 mm, Internal extractor No. 1.30/4.19-25 mm, Internal extractor No. 1.30/4A, 25-30 mm, Internal extractor No. 1.30/45, 30-35 mm, Counter support No. 1.36/1 for 1.30/0 - 1.30/5, Sliding hammer No. 1.35/2, 500 mm, 1.7 kg, + GEDORE L-BOXX® 136 No. 1100 L

### Article information

Contents (Qty of pieces)	<b>8</b>	Exchangeable spindle tip	<b>no</b>
Graduation	<b>no</b>	Can be retrofitted with hydraulic spindle	<b>no</b>
reversible arms available	<b>no</b>	Total length [mm]	<b>444 mm</b>
Net weight [kg]	<b>7,2 kg</b>	Total width [mm]	<b>360 mm</b>
Hook brake available	<b>no</b>	Total height [mm]	<b>152 mm</b>
Hook can be moved parallel	<b>no</b>	Clamping width a2 (min.) internal pulling [mm]	<b>12 mm</b>
Quick release lever available	<b>no</b>	Clamping width a2 (max.) internal pulling [mm]	<b>35 mm</b>
Anti-slip device on the spindle	<b>no</b>		