









Side clip on hood

Style	Ordering number	Cable entry			Description	Outline drawing dimensions in mm
						
		PG	PG	PG		
Cable-to-cable hood bottom entry standard construction						
 	42.70.06.05 42.70.06.79 42.70.06.69 51.42.70.06.05 51.42.70.06.79 51.42.70.06.69	16 16	16 16	16 16	HB.6.KDO-LB.1.16 HB.6.KDO-LB.1.16.Z HB.6.KDO-LB.1.16.G HB-K.6.KDO-LB.1.16 HB-K.6.KDO-LB.1.16.Z HB-K.6.KDO-LB.1.16.G	
high construction  	49.70.16.07 49.70.16.80 49.70.16.70 49.70.16.09 49.70.16.81 49.70.16.71 51.49.70.16.07 51.49.70.16.80 51.49.70.16.70 51.49.70.16.09 51.49.70.16.81 51.49.70.16.71	21 21 29 29	21 21 29 29	21 21 29 29	HD.16.KDO-LB.1.21 HD.16.KDO-LB.1.21.Z HD.16.KDO-LB.1.21.G HD.16.KDO-LB.1.29 HD.16.KDO-LB.1.29.Z HD.16.KDO-LB.1.29.G HD-K.16.KDO-LB.1.21 HD-K.16.KDO-LB.1.21.Z HD-K.16.KDO-LB.1.21.G HD-K.16.KDO-LB.1.29 HD-K.16.KDO-LB.1.29.Z HD-K.16.KDO-LB.1.29.G	